Engineering Specification

Job Name	Contractor
Job Location	Approval
	0.1.1.1.0.0.1
Engineer	Contractor's P.O. No.
Approval	Representative
· ·	·

RD-100-CP15

Roof Drain with 15" x 15" Promenade Top

Specification

Watts RD-100-CP15 epoxy coated cast iron roof drain with flashing clamp with integral gravel stop, 15 5/8" x 15 5/8" square epoxy coated ductile iron promenade top, and no hub (standard) outlet.

Call customer service if you need assistance with technical details.


Pipe Sizing		
Suffix	Description	
2	2"(51) Pipe Size	
3	3"(76) Pipe Size	
4	4"(102) Pipe Size	
5	5"(127) Pipe Size	
6	6"(152) Pipe Size	

Outlet Type		
Suffix	Description	
NH	No Hub (MJ)	
P	Push On	
T	Threaded	
X	Inside Caulk	

Options		
Suffix	Description	
-1	All Nickel Bronze Top	
-6	Vandal Proof Top	
-9	Hinged Grate	
-13	Galvanized Body & Flashing Clamp	
-В	Sump Receiver	
-D	Underdeck Clamp	
-F	Deck Flange/Adj. Extension	
-S0	Side Outlet (2, 3, 4" Only)	

Load	Free Area
Rating	Sq. In.
XHD	57





Deck Opening 10"(254) with Sump Receiver 13 1/4"(337)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

NOTICE

The load classifications are in accordance with the American National Standards ASME A112.6.3 ASME Ratings are as follows:

XHD - Safe Live Load 7500-10,000 lbs.(3375-4500 kg) The above categories are given as a guide only. Please consult factory.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

WATTS

USA: T: (800) 338-2581 • Watts.com **Canada:** T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-RD-100-CP15 2435

