

Engineering Specification



Job Name _____
 Job Location _____
 Engineer _____
 Approval _____
 Tag _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____

RD-940 Downspout Nozzle Specification

Watts RD-940 cast nickel bronze downspout nozzle with anchor flange, countersunk mounting holes, and IPS threaded (standard), no hub, or push-on connection.

Options		
Suffix	Description	
-83	Stainless Steel Bird Screen	<input type="checkbox"/>
-NH	No Hub	<input type="checkbox"/>
-P	Push-On Connection (3, 4, 6, 8" Only) No Add	<input type="checkbox"/>



IPS Threaded Connection

Model	Pipe Size	B	C	D	E	F
RD-942	2"(51)	5 1/4"(133)	2 1/4"(57)	6 3/4"(171)	3 1/2"(89)	4 3/4"(121)
RD-943	3"(76)	5 1/4"(133)	2 1/2"(63)	8 1/4"(210)	3 1/2"(89)	6 3/8"(162)
RD-944	4"(102)	5 1/4"(133)	2 3/4"(70)	9 1/8"(232)	3 1/2"(89)	7"(178)
RD-946	6"(152)	5 1/4"(133)	2 3/4"(70)	11 3/8"(289)	3 1/2"(89)	9"(229)
RD-948	8"(203)	6"(152)	3"(76)	12 1/2"(318)	4"(102)	11"(279)

No Hub Connection

Model	Pipe Size	B	C	D	E	F
RD-942-NH	2"(51)	5 1/4"(133)	2 1/4"(57)	6 3/4"(171)	3 1/2"(89)	4 3/4"(121)
RD-943-NH	3"(76)	5 1/4"(133)	2 1/2"(63)	8 1/4"(210)	3 1/2"(89)	6 3/8"(162)
RD-944-NH	4"(102)	5 1/4"(133)	2 3/4"(70)	9 1/8"(232)	3 1/2"(89)	7"(178)
RD-945-NH	5"(127)	5 1/4"(133)	3"(76)	9 1/4"(235)	3 3/8"(86)	7 1/4"(184)
RD-946-NH	6"(152)	5 1/4"(133)	2 3/4"(70)	11 3/8"(289)	3 1/2"(89)	9"(229)
RD-948-NH	8"(203)	6"(152)	3"(76)	12 1/2"(318)	4"(102)	11"(279)
RD-9410-NH	10"(250)	5 3/4"(146)	3"(76)	15 1/4"(387)	3 3/4"(95)	13 1/16"(332)
RD-9412-NH	12"(305)	6"(152)	3 1/4"(83)	17 1/4"(438)	3 3/4"(95)	15 1/16"(383)

Push-On Connection

Model	Pipe Size	B	C	D	E	F	G	H
RD-943P	3"(76)	5 3/4"(146)	3"(76)	8 1/4"(210)	3 1/2"(89)	6"(152)	1 3/4"(44)	4 3/4"(121)
RD-944-P	4"(102)	5 3/4"(146)	3"(76)	9 1/8"(232)	3 1/2"(89)	6 3/4"(171)	1 3/4"(44)	5 3/4"(146)
RD-946P	6"(152)	6"(152)	3 3/4"(95)	11 3/8"(289)	3 1/2"(89)	8 3/4"(222)	2"(51)	7 3/4"(197)
RD-948P	8"(200)	7"(178)	4"(102)	13 3/8"(340)	34"(864)	10 3/4"(273)	2 1/2"(63)	10"(254)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • F: (828) 248-3929 • Watts.com
Canada: T: (888) 208-8927 • F: (905) 481-2316 • Watts.ca
Latin America: T: (52) 55-4122-0138 • Watts.com