
Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

RD-700

Dual Outlet Roof Drain Overflow Specification

Watts RD-700 epoxy coated cast iron dual outlet roof drain/overflow combination with flashing clamp, integral gravel stop, 4" high internal overflow standpipe, secured ductile iron dome, and no hub outlet(s).



Pipe Sizing		
Suffix	Description	
3	3"(76) Pipe Size	
4	4"(102) Pipe Size	
5	5"(127) Pipe Size	
6	6"(152) Pipe Size	

Options		
Suffix	Description	
-D	Underdeck Clamp	
-F	Deck Flange/Adj. Extension	
-GSS	Stainless Steel Ballast Guard	
-K80	Aluminum Dome	
-K83	SS Mesh Covered Aluminum Dome	
-L	Vandal Proof Dome	
-W2	2" High Overflow	


Free Area Sq. In. 157


Deck Opening: 18 1/2"(470) with Deck Flange 22"(559) x 14"(356)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.







Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

WATTS

USA: T: (800) 338-2581 • Watts.com **Canada:** T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-RD-700 2501 © 2025 Watts