

# Bronze Ball Valves with Stainless Steel Trim

Full Port Design.  
Full Range Sizes.

The G2-SS series offers 2-Piece, Full Port, Lead Free Bronze Ball Valves that are used in commercial and industrial applications for a full range of liquids and gasses. They feature a blowout proof stem and a full-port orifice that minimal pressure drop. The G2-SS Series offers multiple models with solder and NPT end-connections as well as NSF61G certification.

## Features

- Certified NSF 61 for Potable Water applications
- Certified to NSF 372 for Lead Free\* requirements
- 316 Stainless steel ball & stem
- Lead Free\* forged bronze body and adapter
- Full-port flow
- Full range of sizes from 1/4" – 4" (8 – 101.6 mm)
- Minimal pressure drop due to large ports
- Blowout proof, pressure retaining stem
  - Adjustable stem packing gland
- White handles for easy Lead Free\* identification
  - 100% Factory tested in USA
- Used in commercial and industrial applications for a full range of liquids and gases, including potable water

*\*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.*

**Please refer to watts.com for BAA information on specific models.**

LFB6080G2-SS — Threaded

LFB6081G2-SS — Solder



Certified to  
NSF/ANSI 61-G

[Watts.com/ballvalves](http://Watts.com/ballvalves)

**WATTS®**

USA: T: (978) 689-6066 • F: (978) 975-8350 • [Watts.com](http://Watts.com)  
Canada: T: (888) 208-8927 • F: (888) 479-2887 • [Watts.ca](http://Watts.ca)  
Latin America: T: (52) 55-4122-0138 • [Watts.com](http://Watts.com)