

Backflow Preventer Cross Reference Guide

Valve Types	Ames	Watts	Conbraco	FEBCO	Hersey	Wilkins	Cla-Val	Flomatic
SINGLE DETECTOR CHECK VALVE	1000 DCV 4" - 10" 1000SS DCV 4" - 6"	SS07F 4" - 10"	N/A	406, 406D 4" - 10"	DC 2" - 3" EDC 4" - 10" EDC II 8" EDC III 4" - 10" EDC IV 3" - 10"	310 910	N/A	N/A
DOUBLE CHECK VALVE ASSEMBLY	2000B 1/2" - 2" C-200 2 1/2" - 10" C-200N 2 1/2" - 10" 2000SS 2 1/2" - 12" 2000SE 2 1/2" 200B 1/2" - 2" M-200 2 1/2" - 10" M-200N 2 1/2" - 10"	007/U007 1/2" - 3" 709 2 1/2" - 10" 774 2 1/2" - 12" 719 1/2" - 2" 775 1/2" - 2" 757 2 1/2" - 10" 757N 2 1/2" - 10"	40-100 4S-100 2 1/2" - 6"	805YD 2 1/2" - 10" 850 3/4" - 2" 850 4" - 10" 870U 2 1/2" - 10" 857 2 1/2" - 3"	#2 3" - 10" E-1 4" - 6" FDC 3/4" - 2" HDC 3/4" - 2" 2 E-1 FDC HDC	950XL/XLU/XLT 3/4" - 2" 950 2 1/2" - 10" 350 2 1/2" - 8" 450 2 1/2" - 10" 350A 2 1/2" - 10" 350 3/4" - 1"	D-2 D-4 DC6L DC7L DC8L DC8N DC8V	DCV
DOUBLE CHECK DETECTOR ASSEMBLY	3000B 2" C-300 2 1/2" - 10" C-300N 2 1/2" - 10" 3000SS 2 1/2" - 12" 3000SE 2 1/2" M-300 2 1/2" - 10" M-300N 2 1/2" - 10"	007DCDA 2" - 3" 709DCDA 3" - 10" 774DCDA 4" - 12" 757DCDA 2 1/2" - 10" 757NDCDA 2 1/2" - 10"	40-600 3" - 10"	806YD 3" - 10" 856 2 1/2" - 10" 876V 2 1/2" - 10" 858 2 1/2" - 3"	DDC- II 3" - 10" DDC-II	950DA 2 1/2" - 10" 350DA 2 1/2" - 8" 450DA 4" - 10" 350ADA 2 1/2" - 10"	16-4 DD7L DD8L DD8N DD8V	N/A
REDUCED PRESSURE ZONE ASSEMBLY	C-400 2 1/2" - 10" C-400N 2 1/2" - 10" C-400Z 2 1/2" - 10" 4000 SS 2 1/2" - 10" 4000B 1/2" - 2" M-400 2 1/2" - 10" M-400N 2 1/2" - 10" 400B 1/2" - 2"	009 1/4" - 3" 909 3/4" - 10" 994 2 1/2" - 10" 919 1/2" - 2" 957 2 1/2" - 10" 957N 2 1/2" - 10" 957Z 2 1/2" - 10"	40-200 1/2" - 10"	860 3/4" - 2" 825YA 3/4" - 2" 825Y 3/4" - 2" 825YD 2 1/2" - 10" 860 2 1/2" - 10" 880V 2 1/2" - 10" 867 2 1/2" - 3"	FRP II 3/4" - 2" 6CM 2 1/2" - 10"	975XL 3/4" - 2" 975 2 1/2" - 10" 375 475 475V 2 1/2" - 8" 375A 4" - 10" 375 3/4" - 1"	18-4 RP-2 RP-4 RP-4V RP-6L RP-7L RP-8L RP-8N RP-8V	RPZ RPZB
REDUCED PRESSURE DETECTOR ASSEMBLY	C-500 2 1/2" - 10" C-500N 2 1/2" - 10" C-500Z 2 1/2" - 10" 5000 SS 2 1/2" - 10" 5000CIV 2 1/2" - 10" M-500 2 1/2" - 10" M-500N 2 1/2" - 10" M-500Z 2 1/2" - 10"	909RPDA 2 1/2" - 10" 957RPDA 2 1/2" - 10" 957NRPDA 2 1/2" - 10" 957ZRPDA 2 1/2" - 10"	40-700 3" - 10"	826YD 2 1/2" - 10"	6CMDA 4" - 10" 6CM-RPDA	975DA 2 1/2" - 10" 375DA, 475DA, 475DAV 375ADA 4" - 8"	18-4, RD7L	N/A
ATMOSPHERIC VACUUM BREAKERS	A100 1/2" - 2"	188A 3/4" - 2" 288A 1/4" - 3"	38-100 1/4" - 2"	710/715 1/2" - 2"	N/A	35	N/A	N/A
PRESSURE VACUUM BREAKERS	A200 1/2" - 2"	1/2" - 2" 800M4QT 800M4FR	40-500 4V-500	765 1/2" - 2" 767FR 1/2" - 2"	N/A	720 420 720A	N/A	PVB
DUAL CHECK VALVES	20 3/4", 1", 1 1/4"	3/8" - 1 1/4" 07S, 7, Cu7, L7	40-300 4P-300	510 1/2", 3/4"	N/A	700, 705	N/A	810
DUAL CHECK VALVE with Vent	N/A	9D 1/2", 3/4"	40-400 1/2", 3/4"	N/A	N/A	750 1/2", 3/4" 760 1/2", 3/4"	N/A	N/A



Backflow Prevention Products

USA: 815 Chestnut St., No. Andover, MA 01845-6098; www.watts.com

Canada: 5435 North Service Rd., Burlington, ONT. L7L 5H7; www.wattscanada.ca

CR-BP 0732

© Watts Regulator Company, 2007