Engineering Specification

Job Name	Contractor
Job Location	Approval
	0.1.1.1.0.0.1
Engineer	Contractor's P.O. No.
Approval	Representative
· ·	·

RD-270

Scupper Drain with Angle Grate Specification


Watts RD-270 epoxy coated cast iron scupper drain with flashing clamp, secured grate, and no hub (standard) outlet.


Call customer service if you need assistance with technical details.

Pipe Sizing				
Suffix	Description			
2	2"(51) Pipe Size			
3	3"(76) Pipe Size			
4	4"(102) Pipe Size			
6	6"(152) Pipe Size			

Options				
Suffix	Description			
-1	Nickel Bronze Grate & Frame			
-6	Vandal Proof Grate			
-13	Galvanized			
-A	45 Degree Outlet (NH Only)			
-T	Threaded Outlet			







Pipe Size	No Hub		Threaded	
	Α	В	Α	В
2"(51)	5 1/8"(130)	6 1/2"(165)	2 3/4"(70)	6"(152)
3"(76)	4 1/2"(114)	5 3/4"(146)	2 3/4"(70)	5 3/8"(137)
4"(102)	4"(102)	5 1/8"(130)	2 3/4"(70)	4 7/8"(124)
6"(152)	3 1/2"(90)	4 13/16"(122)	N/A	N/A

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

WATTS

USA: T: (800) 338-2581 • Watts.com **Canada:** T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-RD-270 2446 © 2024 Watts