Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

RD-300-AC

Roof Drain with Compression Seal Adjustable Extension Specification

Watts RD-300-AC epoxy coated cast iron roof drain with flashing clamp with integral gravel stop, compression seal adjustable extension assembly, self-locking polyethylene dome (standard), and no hub (standard) outlet.

Call customer service if you need assistance with technical details.


	Pipe Sizing	
Suffix	Description	
2	2"(51) Pipe Size (NH Only)	
3	3"(76) Pipe Size	
4	4"(102) Pipe Size	
5	5"(127) Pipe Size (NH Only)	
6	6"(152) Pipe Size	
8	8"(203) Pipe Size	
10	10"(254) Pipe Size (NH Only)	

Suffix	Description	
NH	No Hub (MJ)	
Р	Push On	
Χ	Inside Caulk	

Free Area Sq. In.
137

Deck Opening: 14 1/2"(368) with Sump Receiver 18"(457)





Options Suffix Description Galvanized Body & Clamp -13 -AC Compression Seal Extension -AE Threaded Extension -B Sump Receiver -D **Underdeck Clamp** -F Deck Flange/Adj. Extension -GSS Stainless Steel Ballast Guard -K **Ductile Iron Dome** -K13 Galvanized Dome -K40 Ductile Iron Low Dome (4" High) -K80 Aluminum Dome -K81 Rough Bronze Dome -K83 SS Mesh Covered Dome -L Vandal Proof Dome -R 2" External Water Dam -W Adj. Internal Water Dam

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

WATTS

USA: T: (800) 338-2581 • Watts.com **Canada:** T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-RD-300-AC 2453 © 2024 Watts