

POWERS™ to POWERS™

Cross Reference - HydroGuard XP Master Tempering Valves

HydroGuard®



HydroGuard® XP



Type	Model 40 - 160°F	Finish	Standard Temp Range 90 - 160°F	Low Temperature Range 60 - 90°F
Master Mixers	431-1000	Rough Bronze	MM431-1	MM431-3
	432-1000	Rough Bronze	MM432-1	MM432-3
	433-1000	Rough Bronze	MM433-1	MM433-3
	434-1000	Rough Bronze	MM434-1	MM434-3
	431-2000	Chrome	MM431-2	MM431-4
	432-2000	Chrome	MM432-2	MM432-4
	433-2000	Chrome	MM433-2	MM433-4
	434-2000	Chrome	MM434-2	MM434-4
Single Valve Hi/Lo <i>WITH outlet thermometer and fittings</i>	1432RB	Rough Bronze	SH1432-11	SH1432-31
	1434RB	Rough Bronze	SH1434-13	SH1434-33
	1432PC	Chrome	SH1432-22	SH1432-42
	1434PC	Chrome	SH1434-24	SH1434-44
Single Valve Hi/Lo <i>LESS outlet thermometer and fittings</i>	1432RB	Rough Bronze	SH1432-1	SH1432-3
	1434RB	Rough Bronze	SH1434-1	SH1434-3
	1432PC	Chrome	SH1432-2	SH1432-4
	1434PC	Chrome	SH1434-2	SH1434-4