

UVT-15 UV Photometer

Accurate %T measurement housed in a rugged, completely self contained case that holds everything needed for measuring the UV %transmission of a sample.

Ordering Information

CATALOG NO.	DESCRIPTION	
19573	UVT-15 UV Photometer 120 volt	
19574	UVT-15 UV Photometer 240 volt	

The UVT-15 UV includes Operating Instruction Decal, Quartz Cuvette and plug in power supply.

Accessories

19313	Quartz Cuvette (package of 2)

Specifications

opeomodions		
Range:	0 - 100% Transmission	
Resolution:	1% Transmission	
Accuracy:	± 2%	
Principle:	Single beam UV filter photometer with pushbutton 100% transmittance control adjustment	
Source:	Low pressure UV Germicidal lamp	
Wavelength Accuracy:	253.7nm	
Path Length:	10mm	
Response Time:	Full scale reading in less that 2 seconds	
Sample Cell:	10mm x 10mm quartz	
Operating Temperature:	0° - 50°C (32° - 122°F)	
Power Supply:	Wall Adapter: 120VAC 60Hz 12W UL & CSA approved 240VAC 50Hz 19VA CE approved	
Display:	3½" Digit LCD Display	
Dimensions:	11"L x 7½"W x 5½"H	
Shipping Dimensions:	11½"L x 8"W x 6"H	
Weight:	4 lbs.	
Shipping Weight:	6 lbs.	

Specifications subject to change without notice.



Standard Features

- Rugged Transportable Carrying Case
 Durability and convenience regardless of sampling location.
- Completely Self-Contained
 Provides easy access to everything needed to take a measurement.
- Simple Calibration Procedures
 Calibration initiated with the push of a button ensures accurate readings



A Watts Water Technologies Company

USA: Tel: (888) 203-7248 • Fax: (239) 332-7643 • HFscientific.com
Latin America: Tel: (52) 81-1001-8600 • Fax: (52) 81-8000-7091 • HFscientific.com