Engineering Specification

Job Name	Contractor Signature
Orion Representative	Approval Date
Quantity Required	Contractor's P.O. No.

12" x 12" x 6" Stainless Steel Floor Sink - Less Grate

12" Sq. x 6" Deep Stainless Steel Sanitary Floor Slnk with Integral FRPP Outlet

Specification

Orion 12" square x 6" deep 14 ga. Type 304 stainless steel sanitary floor sink less grate and no hub outlet. FRPP material conforming to ASTM D4101 or PVDF outlet material conforming to ASTM D3222.




Sizes & Connections

Qty.	FRPP	Qty.	PVDF	Size (in.)	Α
	710173		902217	2	3.58
	710265		902218	3	3.88
	710386		723386	4	3.94
	710486		902219	6	6.37

Stainless Steel Grate Options

Qty.	Part No.	Configuration
	808121	1/2
	808122	3/4
	808120	Full

Qty.	Part No.	Options
	808176	Sediment Bucket
	808174	Flashing Clamp



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Orion product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Orion Technical Service. Orion reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Orion products previously or subsequently sold.

DRION

USA: T: (800) 334-6259 • OrionFittings.com **Canada:** T: (888) 208-8927 • OrionFittings.ca

Latin America: T: (52) 55-4122-0138 • OrionFittings.com

ES-OR-FS-SS6-LG 2410

A WATTS Brand