

Introducing the TR2 Small Diameter Riser

Built with the same Watts precision engineering as the larger diameter Transition Riser (TR), the TR2 is used to connect a 2", 2 1/2", or 3" water supply into the building by passing under the foundation and up through the floor without mechanical joints. The UL Listed, FM Approved, and NSF Certified TR2 replaces numerous fitting, elbows, and spools to reduce the possibility of failures or leaks in comparison to traditional methods and materials, making it ideally suited for fire protection systems.

Higher Integrity

- Single-piece construction removes the mechanical joint beneath the foundation
- Made from corrosion resistant 300 Series stainless steel
- All Watts and Ames risers 100% tested against leaks
- UL Listed, FM Approved, and NSF Certified

Easier Installation

- Eliminates threading, grooving, brazing, and assembling
- Fewer joints to restrain
- Lightweight

Fully Customizable

- 3'-16' leg lengths (not exceeding a combined 19')
- Grooved or Male NPT end connections
- MNPT to FNPT and MNPT to Flange adapters available

Lower Total Cost

- Eliminate labor costs used to construct traditional risers
- Easy and faster installation
- Long and reliable life

Approvals

Fittings FM Class 1920
UL HKQA (2"-10")



Certified to NSF/ANSI 61-G

Transition Risers

Nominal Size	Lengths (Vertical x horizontal)	Connections (Inlet x Outlet)	Ordering Code
2"	4x4	MNPT x MNPT	88006375
	4x4	MNPT x Groove	88006376
	4x4	Groove x Groove	88006377
	4x6	MNPT x MNPT	88006378
	4x6	MNPT x Groove	88006379
	4x6	Groove x Groove	88006380
	6x6	MNPT x MNPT	88006381
	6x6	MNPT x Groove	88006382
2 1/2"	4x4	MNPT x MNPT	88006680
	4x4	MNPT x Groove	88006681
	4x4	Groove x Groove	88006682
	4x6	MNPT x MNPT	88006683
	4x6	MNPT x Groove	88006684
	4x6	Groove x Groove	88006685
	6x6	MNPT x MNPT	88006686
	6x6	MNPT x Groove	88006687
3"	4x4	MNPT x MNPT	88006698
	4x4	MNPT x Groove	88006699
	4x4	Groove x Groove	88006700
	4x6	MNPT x MNPT	88006701
	4x6	MNPT x Groove	88006702
	4x6	Groove x Groove	88006703
	6x6	MNPT x MNPT	88006704
	6x6	MNPT x Groove	88006705
	6x6	Groove x Groove	88006706

Adapters

Nominal Size	Type	Ordering Code
2"	Flange	88008700
	FNPT	88008703
2 1/2"	Flange	88008701
	FNPT	88008704
3"	Flange	88008702
	FNPT	88008418

