

Engineering Specification

Job Name _____
 Job Location _____
 Engineer _____
 Approval _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____

Hand Showers

Part Nos. 141 318N, 141 318WS*, 141 837N

Specifications

Description Professional Hand Shower with 24" Glide Rail Type 7 (*WaterSense® Type 7WS), or 18" Glide Rail Type P

Finish See drawing and table

Agency/Spec Approval . . . IAPMO cUPC
 ASME A112.18.1
 CSA B125.1
 *WaterSense



The products indicated as WaterSense meet LEED® Indoor Water Use Reduction requirements and may help earn a LEED Water Efficiency credit.


Maximum Flow 2.5 gpm (9.5L/min) MAX at 80 psi
 1.8 gpm (6.8L/min) MAX at 80 psi (*WaterSense)

Minimum Flow 1.8 gpm (6.8L/min) MIN at 45psi
 1.4 gpm (5.1L/min) MIN at 45psi (*WaterSense)

Shipping Weight 141 318N, 141 318WS: 2.50 lb (1.14 kg)
 141 837N: 2.47 lb (1.12 kg)



Detail



Call customer support if you need assistance with technical details.

Part Nos. 141 318N, 141 318WS*

ITEM	MODEL	DESCRIPTION	QTY
1	141318AN	Hand Sprayer, Push Button, WHT Plastic, 2.50 GPM	1
2	141161BN	Hose, Stainless Steel, 60 Inches	1
**3	141163DN	Glide Rail, 24", SS, Adjustable Cradle	1
4	141320N	Supply Elbow CP Plastic Cover, Brass ½" NPT	1
*	141318AWS	Hand Sprayer, Push Button, WHT Plastic, 1.80 GPM, WS	1

Part No. 141 837N

ITEM	MODEL	DESCRIPTION	QTY
1	141318AN	Hand Sprayer, Push Button, WHT Plastic, 2.50 GPM	1
2	141161BN	Hose, Stainless Steel, 60 Inches	1
**3	141163EN	Glide Rail, 18", SS, Adjustable Cradle	1
4	141320N	Supply Elbow CP Plastic Cover, Brass ½" NPT	1

**Warning: Never use this product as a grab bar or for support. Personal injury may result if this product is misused.

Powers product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Powers Technical Service. Powers reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Powers products previously or subsequently sold.



USA: Tel: (888) 432-8932 • PowersControls.com
 Canada: Tel: (888) 208-8927 • PowersControls.ca
 Latin America: Tel: (52) 55-4122-0138 • PowersControls.com