

# Engineering Specification

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_

Approval \_\_\_\_\_

Representative \_\_\_\_\_

Tag \_\_\_\_\_


## GX Series Large Capacity Grease Interceptor

### Specifications

Watts Light Commercial GX Series large capacity recessed or floor mounted epoxy coated steel grease interceptor with internal flow control.



Options		
Suffix	Description	
-E	Extension	<input type="checkbox"/>
-THD	Threaded Connections	<input type="checkbox"/>



GX Series

Model #	Flow Rate		Capacity		Pipe Size				Length		Width		Height	
	GPM	LPM	lbs.	kg	A		C		D		E		F	
MODEL					in	mm	in	mm	in	mm	in	mm	in	mm
GX-75	75	283.9	150	68	4	101.6	4½	114.3	39¾	1009.65	30¾	781.05	23	584.2
GX-100	100	378.5	200	90.7	4	101.6	4½	114.3	39¾	1009.65	30¾	781.05	33	838.2
GX-150	150	567.8	300	136	4	101.6	4½	114.3	39¾	1009.65	30¾	781.05	43	1092.2
GX-200	200	757.1	400	181.4	4	101.6	4½	114.3	52	1320.8	34	863.6	43	1092.2
GX-250	250	946.4	500	226.7	6	152.4	6½	165.1	52	1320.8	34	863.6	46	1168.4
GX-300	300	1135.6	600	272.1	6	152.4	6½	165.1	76	1930.4	48	1219.2	48	1219.2
GX-400	400	1514.2	800	362.8	6	152.4	6½	165.1	83	2108.2	55	1397	52	1320.8
GX-500	500	1892.7	1000	453.5	6	152.4	6½	165.1	91	2311.4	60	1524	63	1600.2

### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • F: (828) 248-3929 • Watts.com

Canada: T: (888) 208-8927 • F: (888) 479-2887 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com