Engineering Specification

Job Name	Contractor Signature
Orion Representative	Approval Date
Quantity Required	Contractor's P.O. No.

Please e-mail your signed and completed submittal, tank quote and purchase order to oriontanks@wattswater.com.

T5 Retro-Fit Cylindrical Bolt-On Tank **Extension**

Specification

Orion T5 Retro-Fit Extension shall be cylindrical, seamless, stress and defect free, rotationally molded construction to uniform wall thickness from virgin PE resins conforming to ASTM D 1248. Extension shall include integral anchor flange for bolting and gasketing to existing tank. Standard, non-load bearing, domed tank cover shall be bolted and gasketed to tank extension.

Extension Tank Size


SELECTION	BASE TANK CAPACITY	EXT. HT. (IN)		
(CHECK ONE)	(USG)	MIN.	MAX.	COVER
		(A)	(A)	DIA. (IN.)
	5	4	13	14
	15	4	12.25	20.5
	30	4	25.5	20.5
	55	4	29	26
	100	4	44	27.25
	150	4	44.5	34.5
	180	4	34.5	40
	200	4	45.25	41.25
	275	4	39	44.75
	360	4	39.75	51.75
	500	4	48	57
	600	4	58	53
	1200	4	36	74


CONNECTION, COVER, SUPPORT & ACCESS OPTIONS						
	Tank Anchor Flange		4" Cleanout Access			
	Reinforcing Anchor Flange		6" Cleanout Access			
	Fiberglass Wrap*		12" Gamma Top Access			
	3/4" Plastic Cover		16" Gamma Top Access			
	1/4" Steel x 3/4" Plastic Cover		20" x 3/4" Bolted Access			
	(Not to be used in conjunction w/Access Options)		24" x 3/4" Bolted Access			

CALIFORNIA PROP 65 WARNING: This product can expose you to chemicals including benzene which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

USA: T: (800) 334-6259 • OrionFittings.com

Canada: T: (888) 208-8927 • OrionFittings.ca





Side View

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Please verify all selections with your local Orion rep - tank products and accessory equipment are non-returnable.

Orion Fittings product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Orion Fittings Technical Service. Orion Fittings reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Orion Fittings products previously or subsequently sold.

A WATTS Brand

Latin America: T: (52) 55-4122-0138 • OrionFittings.com

© 2024 Watts