Engineering Specification

Job Name	Contractor
Job Location	Approval
	πρριοναι
Engineer	Contractor's P.O. No.
Approval	Representative
Too	

FS-900


12" x 24" Sanitary Floor Receptor


Specification

Watts FS-900 12"(305) square x 24"(610) white acid resistant coated fabricated steel sanitary floor receptor with flange, nickel bronze or ductile iron grates, dome bottom strainer, and no hub (standard) outlet.

Pipe Sizing		
Suffix	Description	
2	2"(51) Pipe Size	
3	3"(76) Pipe Size	
4	4"(102) Pipe Size	
6	6"(152) Pipe Size	

Outlet Type			
Description			
No Hub (MJ)			
Push-On			
	Description No Hub (MJ)		





Options				
Suffix	Description			
-FC	Flange w/Weepholes & Flashing Clamp			
-5	Sediment Bucket			
-6	Vandal Proof			
-33	Less Grate			
-150	1/2 Grate			
-175	3/4 Grate			
-F4-1	4" Round Nickel Bronze Funnel			
-F6-1	6" Round Nickel Bronze Funnel			
-G-1	4x9" Oval Nickel Bronze Funnel			

Load	Free Area
Rating	Sq. In.
MD*	125

NOTICE

The load classifications are in accordance with the American National Standards ASME A112.21.1M ASME Ratings are as follows:

MD* - Safe Live Load 2000-4999 lbs. (900-2250 kg) The above categories are given as a guide only.

Please consult factory.

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



ES-WD-FS-900 2127 © 2021 Watts