

Engineering Specification

Job Name _____
 Job Location _____
 Engineer _____
 Approval _____
 Tag _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____

OI-K Large Capacity Oil Interceptor




Specification

Watts OI-K Series recessed or floor mounted epoxy coated steel oil interceptor with gasketed epoxy coated steel skid-proof cover secured with hex head center bolt(s), double wall deep seal trap, 2" IPS oil draw-off connection and 2"(51) no hub dual vent connections, internal stainless steel flow control plate, and no hub (standard) inlet and outlet connections

Flow Rate	
Size	Description
75	75 GPM
100	100 GPM
150	150 GPM
200	200 GPM
250	250 GPM
300	300 GPM
400	400 GPM
500	500 GPM

Options	
Suffix	Description
-B	Sediment Bucket
-E	Extension
-FC	Flange & Clamp Device
-HD	Heavy Duty (10,000 lb.) Traffic Cover*
-O	Inlet & Outlet other than Standard Size
-SS	Stainless Steel
-THD	Threaded Connections

* HD Option Requires Minimum 3" Ext.



Interceptor	Flow	A	C	D	E	F	G	H	J	K
Catalog	Rate	Inlet &	Top to				Base to			
Number	GPM	Outlet	Center	Length	Width	Height	Center			
OI-75-K	75	4"(102)	4 1/2"(114)	39 3/4"(1010)	30 3/4"(781)	23"(584)	9 1/2"(241)	21 3/4"(552)	8"(203)	7"(178)
OI-100-K	100	4"(102)	4 1/2"(114)	39 3/4"(1010)	30 3/4"(781)	33"(838)	19 1/2"(495)	21 3/4"(552)	8"(203)	7"(178)
OI-150-K	150	4"(102)	4 1/2"(114)	39 3/4"(1010)	30 3/4"(781)	43"(1092)	29 1/2"(749)	21 3/4"(552)	8"(203)	7"(178)
OI-200-K	200	4"(102)	6 1/2"(165)	52"(1321)	34"(864)	43"(1092)	18 1/2"(470)	41"(1041)	8"(203)	7"(178)
OI-250-K	250	4"(102)	6 1/2"(165)	52"(1321)	34"(864)	46"(1168)	30 1/2"(775)	45"(1143)	8"(203)	7"(178)
OI-300-K	300	6"(152)	10"(254)	76"(1930)	48"(1219)	48"(1219)	28"(711)	48"(1219)	12"(305)	10"(254)
OI-400-K	400	6"(152)	10"(254)	83"(2108)	55"(1397)	52"(1321)	32"(813)	52"(1321)	12"(305)	10"(254)
OI-500-K	500	6"(152)	10"(254)	91"(2311)	60"(1524)	63"(1600)	43"(1092)	63"(1600)	12"(305)	10"(254)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com