

Engineering Specification

Job Name _____
 Job Location _____
 Engineer _____
 Approval _____
 Tag _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____


GI-K Large Capacity Grease Interceptor Specification:

Watts Drainage GI-K Series recessed or floor mounted epoxy coated steel grease interceptor with gasketed epoxy coated steel skid-proof cover secured with hex head center bolt(s), double wall deep seal trap, integral stainless steel flow control plate, and no hub (standard) connections.



Flow Rate Suffix	Flow Rate Description		Suffix	Options Description	
75	75 GPM	<input type="checkbox"/>	-B	Sediment Bucket	<input type="checkbox"/>
100	100 GPM	<input type="checkbox"/>	-E	Extension	<input type="checkbox"/>
150	150 GPM	<input type="checkbox"/>	-FC	Flange & Clamp Device	<input type="checkbox"/>
200	200 GPM	<input type="checkbox"/>	-HD	Heavy Duty (10,000 lb.) Traffic Cover*	<input type="checkbox"/>
250	250 GPM	<input type="checkbox"/>	-O	Inlet & Outlet other than Standard Size	<input type="checkbox"/>
300	300 GPM	<input type="checkbox"/>	-SS	Stainless Steel	<input type="checkbox"/>
400	400 GPM	<input type="checkbox"/>	-THD	Threaded Connections	<input type="checkbox"/>
500	500 GPM	<input type="checkbox"/>			

*-HD Option Requires Minimum 3" Extension



INTERCEPTOR CATALOG NUMBER	FLOW RATE GPM	GREASE CAPACITY LBS.	A INLET & OUTLET	B BASE TO CENTER	C TOP TO CENTER	D LENGTH	E WIDTH	F HEIGHT
GI-75-K	75	150	4"(102)	18-1/2"(470)	4-1/2"(114)	39-3/4"(1010)	30-3/4"(781)	23"(584)
GI-100-K	100	200	4"(102)	28-1/2"(724)	4-1/2"(114)	39-3/4"(1010)	30-3/4"(781)	33"(838)
GI-150-K	150	300	4"(102)	38-1/2"(978)	4-1/2"(114)	39-3/4"(1010)	30-3/4"(781)	43"(1092)
GI-200-K	200	400	4"(102)	36-1/2"(927)	6-1/2"(165)	52"(1321)	34"(864)	43"(1092)
GI-250-K	250	500	4"(102)	39-1/2"(1003)	6-1/2"(165)	52"(1321)	34"(864)	46"(1168)
GI-300-K	300	600	6"(152)	38"(965)	10"(254)	76"(1930)	48"(1219)	48"(1219)
GI-400-K	400	800	6"(152)	42"(1067)	10"(254)	83"(2108)	55"(1397)	52"(1321)
GI-500-K	500	1000	6"(152)	53"(1346)	10"(254)	91"(2311)	60"(1524)	63"(1600)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • F: (828) 248-3929 • Watts.com
Canada: T: (888) 208-8927 • F: (905) 481-2316 • Watts.ca
Latin America: T: (52) 55-4122-0138 • Watts.com