

Engineering Specification

Job Name _____
 Job Location _____
 Engineer _____
 Approval _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____


WD Series PDI Certified Grease Interceptor Specification

Watts WD Series PDI Certified recessed or floor mounted epoxy coated steel grease interceptor with gasketed skid-proof cover secured with hex head center bolt(s), removable baffle assembly, deep seal trap with cleanout and air relief bypass, external vented flow control fitting, and no hub (standard) connections.



Call customer service if you need assistance with technical details.

Flow Rate		
Suffix	Description	
4	4 GPM	<input type="checkbox"/>
7	7 GPM	<input type="checkbox"/>
10	10 GPM	<input type="checkbox"/>
15	15 GPM	<input type="checkbox"/>
20	20 GPM	<input type="checkbox"/>
25	25 GPM	<input type="checkbox"/>
35	35 GPM	<input type="checkbox"/>
50	50 GPM	<input type="checkbox"/>



Options		
Suffix	Description	
-B	Sediment Bucket	<input type="checkbox"/>
-E	Extension	<input type="checkbox"/>
-FC	Flange & Clamp Device	<input type="checkbox"/>
-HD	Heavy Duty (10,000 lb.) Traffic Cover*	<input type="checkbox"/>
-O	Inlet & Outlet (other than Standard)	<input type="checkbox"/>
-SS	Stainless Steel	<input type="checkbox"/>
-THD	Threaded Connections	<input type="checkbox"/>

*HD Options Requires Minimum 3" Extension

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



Dimensional Chart

Model No.	Flow Rate GPM	Grease Capacity Lbs.	A Inlet & Outlet	B Base To Center	C Top To Center	D Length	E Width	F Height
WD-4	4	8	2"(51)	7 3/4"(216)	3 1/4"(83)	16"(406)	10"(254)	11"(279)
WD-7	7	14	2"(51)	8 1/2"(216)	3 1/2"(89)	18"(457)	13"(330)	12"(305)
WD-10	10	20	2"(51)	8 1/2"(216)	3 1/2"(89)	21 3/4"(552)	14"(356)	12"(305)
WD-15	15	30	2"(51)	10 1/2"(267)	3 1/2"(89)	22"(559)	15"(381)	14"(356)
WD-20	20	40	3"(76)	11 1/2"(292)	3 1/2"(89)	24"(610)	15 3/4"(400)	15"(381)
WD-25	25	50	3"(76)	12"(305)	4 1/2"(114)	26"(660)	16 1/2"(419)	16 1/2"(419)
WD-35	35	70	3"(76)	14"(356)	5"(127)	30"(762)	18"(457)	19"(483)
WD-50	50	100	4"(102)	16"(406)	5 1/2"(140)	32"(813)	22"(559)	21 1/2"(546)



USA: T: (800) 338-2581 • Watts.com
Canada: T: (888) 208-8927 • Watts.ca
Latin America: T: (52) 55-4122-0138 • Watts.com

