

Engineering Specification

CHEXTER SELECTION GUIDE (BY CATALOG NO.)

CATALOG NO.	TYPE	RATING	FACING	SIZE RANGE	BODY MATERIAL
1600	D	125 Class	RF	2-36"	Cast Iron
1601	A	150 Class	RF	2-30"	Carbon Steel
1601	C	150 Class	RF	2-12"	Stainless Steel
1602	D	250 Class	RF	2-24"	Cast Iron
1603	A	300 Class	RF	2-24"	Carbon Steel
1603	C	300 Class	RF	2-12"	Stainless Steel
1604	A	400 Class	RF	2-24"	Carbon Steel
1605	A	600 Class	RF	2-24"	Carbon Steel
1605	C	600 Class	RF	2-12"	Stainless Steel
1606	A	900 Class	RF	2-12"	Carbon Steel
1606	C	900 Class	RF	2-12"	Stainless Steel
1607	A	1500 Class	RF	2-4"	Carbon Steel
1645	A	600 Class	RTJ	2-12"	Carbon Steel
1645	C	600 Class	RTJ	2-12"	Stainless Steel
1646	A	900 Class	RTJ	2-12"	Carbon Steel
1646	C	900 Class	RTJ	2-12"	Stainless Steel
1696	A	2000 Lb. API	RTJ	2-4"	Carbon Steel
1697	A	3000 Lb. API	RTJ	2-4"	Carbon Steel

CHEXTER SELECTION GUIDE (BY BODY MATERIAL)

CATALOG NO.	TYPE	RATING	FACING	SIZE RANGE	BODY MATERIAL
1600	D	125 Class	RF	2-36"	Cast Iron
1602	D	250 Class	RF	2-24"	Cast Iron
1601	A	150 Class	RF	2-30"	Carbon Steel
1603	A	300 Class	RF	2-24"	Carbon Steel
1604	A	400 Class	RF	2-24"	Carbon Steel
1605	A	600 Class	RF	2-24"	Carbon Steel
1606	A	900 Class	RF	2-12"	Carbon Steel
1607	A	1500 Class	RF	2-4"	Carbon Steel
1645	A	600 Class	RTJ	2-12"	Carbon Steel
1646	A	900 Class	RTJ	2-12"	Carbon Steel
1696	A	2000 Lb. API	RTJ	2-4"	Carbon Steel
1697	A	3000 Lb. API	RTJ	2-4"	Carbon Steel
1601	C	150 Class	RF	2-12"	Stainless Steel
1603	C	300 Class	RF	2-12"	Stainless Steel
1605	C	600 Class	RF	2-12"	Stainless Steel
1606	C	900 Class	RF	2-12"	Stainless Steel
1645	C	600 Class	RTJ	2-12"	Stainless Steel
1646	C	900 Class	RTJ	2-12"	Stainless Steel

Limited Warranty: Mueller Steam Specialty warrants each product to be free from defects in material and workmanship under normal usage for a period of one year from the date of original shipment. In the event of such defects within the warranty period, the Company will, at its option, replace or recondition the product without charge. This shall constitute the sole and exclusive remedy for breach of warranty, and the Company shall not be responsible for any incidental, special or consequential damages, including without limitation, lost profits or the cost of repairing or replacing other property which is damaged if this product does not work properly, other costs resulting from labor charges, delays, vandalism, negligence, fouling caused by foreign material, damage from adverse water conditions, chemical, or any other circumstances over which the Company has no control. This warranty shall be invalidated by any abuse, misuse, misapplication or improper installation of the product. **THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** Any implied warranties that are imposed by law are limited in duration to one year.

Some States do not allow limitations on how long an implied warranty lasts, and some States do not allow the exclusion or limitation of incidental or consequential damages. Therefore the above limitations may not apply to you. This Limited Warranty gives you specific legal rights, and you may have other rights that vary from State to State. You should consult applicable state laws to determine your rights.



A WATTS Brand

USA: T: (800) 334-6259 • F: (800) 421-6772 • MuellerSteam.com

Latin America: T: (52) 55-4122-0138 • MuellerSteam.com