

## ACV Schematic

# LEAD FREE\*

## 910-15GS (Globe)

### Pressure Reducing Control Valve with Solenoid (On-Off) Feature

#### Features

- Throttles to reduce high upstream pressure to constant lower downstream pressure
- Solenoid (On-Off) Feature provides electrical override of valve function
- Reducing setpoint is adjustable

#### Standard Components

- 1 - Main Valve (905GS - Single Chamber)
- 2 - Pressure Reducing Control
- 3 - 2-Way Solenoid
- 4 - Fixed Orifice
- X - Isolation Cocks


#### Options and Accessories

- FC - Flo-Clean Strainer
- Y - Y-Strainer (Replaces Flo-Clean)
- ACS - Adjustable Closing Speed (Replaces Fixed Orifice)
- AOS - Adjustable Opening Speed
- P – Position Indicator
- L – Limit Switch

#### Operation

The ACV Combination Pressure Reducing and Solenoid On-Off Control Valve is designed to automatically reduce a fluctuating higher upstream pressure to a constant lower downstream pressure regardless of varying flow rates, and open, allowing regulating action, or close drip-tight as commanded by the Solenoid Pilot. It is controlled by a normally open, pressure reducing pilot designed to: 1) Open (allowing fluid out of the main valve cover chamber) when downstream pressure is below the adjustable setpoint, and 2) Close (allowing fluid to fill the main valve cover chamber) when downstream pressure is above the adjustable setpoint. A decrease in downstream pressure causes the valve to modulate toward an open position, raising downstream pressure. An increase in downstream pressure causes the valve to modulate toward a closed position, lowering downstream pressure.

The Solenoid Pilot will either open to allow regulating action, or close the valve drip-tight when energized. Specify energize to open or close the Main Valve and voltage PRIOR to ordering.



\*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

#### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Ames Fire & Waterworks product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Ames Fire & Waterworks Technical Service. Ames Fire & Waterworks reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Ames Fire & Waterworks products previously or subsequently sold.

**USA: Backflow** Tel: (978) 689-6066 • Fax: (978) 975-8350 • AmesFireWater.com  
**USA: Control Valves** Tel: (713) 943-0688 • Fax: (713) 944-9445 • AmesFireWater.com  
**Canada:** Tel: (905) 332-4090 • Fax: (905) 332-7068 • AmesFireWater.ca  
**Latin America:** Tel: (52) 81-1001-8600 • Fax: (52) 81-8000-7091 • AmesFireWater.com

SCH-A-ACV-910-15GS 1626



**A WATTS Brand**

© 2016 Ames Fire & Waterworks