

tekmar® Submittal

Actuating Motor 742




742_C
10/13

Accessories Replaces: 08/13

Job _____ Designer _____ Contact _____

The Actuating Motor 742 uses a 0-10 or 2-10 V (dc) signal to adjust the position of a mixing valve. It is compatible with tekmar brass mixing valves 710 to 724. It provides 88 in•lbs (10 N•m) of torque over a 90° rotation. The rotation direction is selected by a toggle switch.



Specifications

| Actuating Motor 742 0-10 V (dc) | |
|---------------------------------|--|
| Literature | 742_C, 742_D |
| Packaged weight | 1.1 lbs (500 g) |
| Dimensions | 3-5/8" H x 3-1/8" W x 3-9/16" D (93 x 80 x 90 mm) |
| Enclosure | Polycarbonate plastic, NEMA type 1 |
| Ambient conditions | Indoor use only, 32 to 122°F (0 to 50°C), 95% RH non-condensing |
| Power supply | 24 V ± 10% (ac/dc), 2.5 VA, Class 2 |
| Control signal input | 0-10 V (dc) or 2-10 V (dc), selected by switch setting, 100 kΩ maximum input impedance |
| Position signal output | 0-10 V (dc) or 2-10 V (dc), follows switch setting, 3 kΩ maximum load impedance |
| Angle of rotation | Electrically limited to 90° shaft rotation, clockwise or counterclockwise direction selected by switch setting |
| Motor speed | 140 seconds |
| Rated torque | 88 in•lbs (10 N•m) |
| Warranty | Limited 3 Year (See 742_D for full warranty) |

Additional Features

- Manual override dial
- Reversible scale plate



tekmar Control Systems Ltd., A Watts Water Technologies Company. Head Office: 5100 Silver Star Road, Vernon, B.C. Canada V1B 3K4, 250-545-7749, Fax. 250-545-0650 Web Site: www.tekmarControls.com

