

Micro 100 Laboratory Turbidimeter

Designed to provide the accuracy demanded by today's scientist, the Micro 100 Laboratory

Designed to provide the accuracy demanded by today's scientist, the Micro 100 Laboratory Turbidimeter is ready to meet the challenge. Features such as the Auto Alert Calibration Prompt and the Quick Connection Lamp Module, allow for simple calibration and low maintenance. With a resolution of 0.01 NTU at low turbidity readings and an extended range to 1,000 NTU, the Micro 100 is an ideal and affordable tool for research as well as routine analytical measurements.

Standard Features

Auto Ranging 0 - 1000 NTU
 Instrument senses turbidity level of sample and automatically adjusts to the appropriate measurement.

Auto Alert Calibration Prompt

Automatically prompts the operator when calibration of the instrument is needed.

• Simple Calibration Procedures

Calibration initiated with the push of a button ensures accurate readings

RS-232 Output

Date, time and NTU reading can be captured with a serial printer or data recorder.

Optional Features

Infrared Light Source Micro 100 IR
 Meets international standard ISO 7027 for turbidity measurement.

• Pour Through Assembly

Save time by pouring your grab sample through the measurement chamber.

• Reusable *ProCal* Calibration Standards

Quick and easy calibration across all ranges without the need to mix Formazin

Ordering Information

Cat. No.	Description	
20001	Micro 100 Laboratory Turbidimeter, 120 VAC	
19950	Micro 100 Laboratory Turbidimeter, 100 - 240 VAC	
19952	Micro 100 IR Laboratory Turbidimeter, 100 - 240 VAC	

All units include a set of ProCal Calibration Standards (0.02, 10, and 1,000 NTU), two measuring cuvettes with light shield caps, operator's manual, and plug-in power adapter.

Accessories

19975	Pour Through Assembly	
39957	ProCal Calibration Set, (0.02, 10, & 1000 NTU)	
50051	Cuvettes, 28 x 70mm, 3 pack	
50052	Cuvettes, 28 x 70mm, 10 pack	
50040	Formazin Stock Solution Kit	

Specifications

Range:	Auto Ranging from 0 - 1000 NTU		
Measurement Principle:	Nephelometric non-ratio		
Accuracy:	± 2% of reading plus 0.01 NTU whichever is greater		
Resolution:	0.01 NTU (0 -9.99 NTU) 0.1 NTU (10 - 99.9 NTU) 1 NTU (100 - 1000 NTU)		
Response Time:	≤ 6 seconds		
Sample Size:	30 ml (27ml minimum)		
Light Source:	Quick Connect Tungsten Filament or Infrared		
Operating Temperature:	32° - 122°F (0° - 50°C)		
Outputs:	RS-232 Printer Port		
Dimensions:	10.75 x 10 x 3.75 in. (27.3 x 25.4 x 9.5 cm)		
Weight:	2.9 lbs. (1.32 kg)		
Safety rating:	UL, CSA, CE		

Note: The Micro 100 meets performance criteria specified by USEPA method 180.1 for NTU measurement and ISO7027 (IR version).

Specifications subject to change without notice.



Optional Pour Through Assembly