Engineering Specification

Job Name —————	Contractor —
Job Location ————	Approval —————
Engineer ———————————————————————————————————	Contractor's P.O. No.
Approval —————	Representative ————

LEAD FREE*

MasterSeries® LF860 Large

Reduced Pressure Zone Backflow Prevention Assembly

21/2" - 10"

MasterSeries LF860 Reduced Pressure Zone assembly is designed to protect against backpressure and backsiphonage conditions for high hazard/toxic application in accordance with Local Governing Water Utility Code. Used primarily on potable drinking water systems where Local Governing Code mandates protection from non-potable quality water being pumped or siphoned back into the potable water system.

The ductile iron body is fused with ArmorTek® coating technology to resist corrosion due to microbial induced corrosion (MIC) or exposed metal substrate. The series features Lead Free construction to comply with low lead installation requirements. The Lead Free Reduced Pressure Zone assemblies shall comply with state codes and standards, where applicable, requiring reduced lead content.

The series include a flood sensor to detect excessive water discharges from the relief valve. The flood sensor relays a signal that triggers a multichannel alert (call, email, text) to notify personnel about potential flooding.

NOTICE

An add-on connection kit is required to activate the flood sensor. Without the connection kit, the flood sensor is a passive component that does not communicate with any other device. (A retrofit sensor connection kit is also available for existing installations. For more information, download RP/IS-F-860RP/RPDA.)

NOTICE

Use of the flood sensor does not replace the need to comply with all required instructions, codes, and regulations related to installation, operation, and maintenance of this product, including the need to provide proper drainage in the event of a discharge.

Watts $^{\tiny \circledR}$ is not responsible for the failure of alerts due to connectivity issues, power outages, or improper installation.



LF860-OSY with flood sensor

Features

- Stainless steel relief valve seat and stainless steel check components for maximum performance and durability
- Inline serviceable assembly
- · No special tools required for servicing
- Captured modular spring assembly
- Reversible and replaceable discs
- Field replaceable seats
- Ductile iron valve body design
- Advanced ArmorTek coating technology to resist corrosion of internals
- Modular and repairable pressure differential relief valve
- Clapper check assembly
- Captured O-ring design
- Sensor on relief valve for flood detection, activated by add-on connection kit for BMS or cellular network communication

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Inquire with governing authorities for local installation requirements.



^{*}The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Specification

FEBCO MasterSeries LF860 Reduced Pressure Zone assembly shall be installed on the potable water supply and at each point of cross-connection to protect against possible backpressure and backsiphonage conditions for high hazard/toxic applications. The assembly shall consist of a main line valve body composed of a pressure differential relief valve located in a zone between two (2) independently acting approved clapper style check modules with replaceable seats and disc rubbers. Servicing of the pressure differential relief valve and both check modules does not require any special tools; both check modules are accessed through independently top entry covers. This assembly shall be fitted with AWWA Compliant inlet/outlet resilient seated shutoff valves; when used on a Fire-Sprinkler application, the assembly shall be fitted with UL Classified and FM Approved inlet/outlet resilient seated shutoff valves and contain four (4) properly located resilient seated test cocks as specified by AWWA Standard C511. The valve body shall incorporate a coating system with built-in electrochemical corrosion inhibitor and microbial inhibitor. Flow and pressure loss performance parameters shall meet the requirements of AWWA Standard C511. The assembly shall be FEBCO MasterSeries LF860 Large and shall include a sensor on the relief valve for flood detection.

Model/Option

FS Sensor on the relief valve for flood detection

OSY UL Classified and FM Approved OS&Y gate valves

(ANSI/AWWA C515 Compliant)

NRS Non-rising stem gate valves

(ANSI/AWWA C509 Compliant)

LG Less shutoff valves (This is NOT an APPROVED

ASSEMBLY.)

Example Ordering Descriptions

4" LF860-OSY-FS - Valve assembly fitted with OS&Y shutoff valves and flood sensor

4" LF860-NRS-FS - Valve assembly fitted with NRS shutoff valves and flood sensor

Approvals - Standards

- Approved by the Foundation for Cross-Connection Control and Hydraulic Research at The University of Southern California (FCCCHR-USC)
- ASSE 1013 Listed
- UL Classified** (US & Canada)
- FM Approved**
- IAPMO
- AWWA Standard C511 Compliant
- End Connections: Compliant to ASME B16.1 Class 125 & AWWA Class D Flange













Assembly Flow Orientation

Horizontal (2½" - 10") - Approved by FCCCHR-USC, ASSE, cULus, FM, IAPMO, and CSA

^{**}Assembly configured with UL Classified and FM Approved OS&Y RW gate valves. Less gate valve assemblies are not UL Classified and FM Approved configurations.

Materials

All assemblies (sizes $2\frac{1}{2}$ " to 10") are similar in materials and construction. Contact your local FEBCO representative if you require further information.

Main Valve Body Ductile iron Grade 65-45-12 Relief Valve Body Ductile iron Grade 65-45-12

Coating Fusion epoxy coated internal and external

AWWA C550

Shutoff Valves NRS resilient wedge gate valve AWWA C509

(Standard)

OSY resilient wedge gate valve AWWA C515

(UL Classified and FM Approved)

Check Seats Stainless steel
Relief Valve Seat Stainless steel
Disc Holder Stainless steel
Elastomer Disc Silicone
Spring Stainless steel


Clamp AWWA C606 (10" only)

Pressure - Temperature

Max. Working Pressure175 psi (12.1 bar)Min. Working Pressure20 psi (1.4 bar)Hydrostatic Test Pressure350 psi (24.1 bar)Hydrostatic Safety Pressure700 psi (48.3 bar)


Temperature Range $33^{\circ}F - 140^{\circ}F (0.5^{\circ}C - 60^{\circ}C)$

continuous



Dimensions and Weights

Below are the nominal dimensions and physical weights for LF860 Large, sizes $2\frac{1}{2}$ " to 10". Allowances must be made for normal manufacturing tolerances. Download installation instructions at watts.com, or contact your local FEBCO representative for more information.



Call customer service if you need assistance with technical details.

SIZE	DIMENSIONS														WEIGHT***					
	Α		ВС		D		E*		F**		G		Н		NRS		OSY			
in.	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lb	kg	lb	kg
21/2	40¾	1035	25½	648	10	254	11%	288	125/8	321	16¾	416	41/2	114	71//8	181	250	113	254	115
3	417/8	1064	25%	651	10	254	11%	288	127/8	327	221/4	565	41/2	114	7%	187	276	125	280	127
4	461/4	1175	28	711	101//	257	11½	291	14%	365	231/4	591	5½	140	81//8	206	335	152	347	157
6	56	1422	34¾	883	123/4	324	121/2	316	187/8	479	301//8	765	61/2	165	97/8	251	503	228	523	237
8	65	1651	41¾	1061	15%	397	13%	345	231/2	597	37¾	959	7	178	111//	283	807	366	835	379
10	725/8	1845	463/8	1178	15%	397	13¾	348	271/2	699	48	1219	9	229	12%	314	1205	547	1243	564

^{*} Indicates nominal dimensions with NRS gate valves.

The gap drain is not designed to catch the maximum discharge possible from the relief valve. The installation of the FEBCO air gap with the drain line terminating above a floor drain handles any normal discharge or nuisance spitting through the relief valve. However, floor drain size may need to be designed to prevent water damage caused by a complete failure condition. Do not reduce the size of the drain line from the air gap fitting.

^{**} Indicates nominal dimensions with OSY gate valves (full open position).


^{***} Indicates weight of complete backflow assemblies with specified gate valves.


Performance


The flow capacity chart identifies valve performance based upon rated water velocity up to 20 fps.


- Maximum service flow rate is determined by maximum rated velocity of 7.5 fps.
- AWWA Manual M-22 (Appendix C) recommends that the maximum water velocity in the services be not more than 10 fps.
- UL flow rate is determined by typically rated velocity of 15 ft/s.


Capacity
















USA: T: (800) 767-1234 • FEBCOonline.com
Canada: T: (888) 208-8927 • FEBCOonline.ca
Latin America: T: (52) 55-4122-0138 • FEBCOonline.com

ES-F-LF860L 2435 ©2024 Watts