Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

QTK7-101-L/R

QT QuickTurn™ Single Horizontal Adjustable Closet Carrier, Partially Assembled Specification

Watts QTK7-101-L/R QuickTurn™ single horizontal adjustable water closet carrier with 4" (102) No Hub epoxy coated cast iron fitting, Integral 2" (51) vent connections, labor saving partially assembled faceplate pre-set to a 7-1/2" (ADA) roughin and epoxy coated cast iron feet with incremental height markings, 4" (102) adjustable ABS nipple with integral test car fabricated steel tiling plate, neoprene compression gasket and chrome plated hardware. Carrier complies with the requirements of ASME A112.6.1M up to a 500 lb. (227 kg) static loa

3	3 11/16" (94)			Rear Anchor Support						
	Ī				0		/2"(5	1) Vent	Ī	
	+									
		3/4"				7]	ı	
	(137) 1	(44) 1							1 13/16" 3 13/16"	
		<u> </u>					<u>ת</u> כ_	') 10/10 1 	viax.
	_	<u> </u>						A		
g	Ţ	T						2" (51)		
٦-	1" N 6" N							(51)		
20	Ĭ] .] .		
ap,	-	///4		30/111111		** **********************************	<u> </u>	// -		
nd	Ī				6 5/8"					
1	5/1		0.0/48		(168)					
ad.	(8)	2 3/4" ₋ (70)	-	→	10 1/4	!" -	-		
		-	◄ (70)	17 3		(260)				
		ı		(45	51)		ı			





7 1/2" Pre-Set Faceplate Assembly Kit



Shown Fully Assembled (Includes Kit & Required Fitting)

18 3/8' (467)9" (229)5 3/8" 7 1/2" (137)17 3/4" (191) (451)4 1/2" Min. 9 3/4" Max. 4 1/2' (114) 3 5/16" Min. 1/2"(13) 6 1/2" Max. Tapped Hole

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

USA: T: (800) 338-2581 • F: (828) 248-3929 • Watts.com Canada: T: (888) 208-8927 • F: (888) 479-2887 • Watts.ca Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-QTK7-101-L/R 2219