Engineering Specification

| Job Name | Contractor |
|--------------|-----------------------|
| Job Location | Approval |
| Engineer | Contractor's P.O. No. |
| Approval | Representative |

FD-1100-A-LR

Floor Drain with Ligature Resistant Round Strainer

Specification

Watts FD-1100-A-LR epoxy coated cast iron drain body and anchor flange with fabricated stainless steel ligature resistant strainer. No hub (standard) outlet and vandal proof screws standard.

Call customer service if you need assistance with technical details.

| Pipe Sizing | | |
|-------------|-----------------------------|--|
| Suffix | Description | |
| 2 | 2"(51) Pipe Size | |
| 3 | 3"(76) Pipe Size | |
| 4 | 4"(102) Pipe Size | |
| 6 | 6"(152) Pipe Size (NH Only) | |

| Outlet Type | | |
|-------------|-------------|--|
| Suffix | Description | |
| NH | No Hub (MJ) | |
| P | Push On | |

| Strainer Size | | |
|--------------------|------------------------------|--|
| Suffix Description | | |
| A5 | 5"(127) Dia. Stainless Steel | |
| A6 | 6"(152) Dia. Stainless Steel | |
| A8 | 8"(203) Dia. Stainless Steel | |

| Options | | |
|---------|------------------------------------|--|
| Suffix | Description | |
| -5 | Sediment Bucket | |
| -6 | Vandal Proof | |
| -7 | Trap Primer Tapping | |
| -8 | Backwater Valve (2, 3, 4" Only) | |
| -13 | Galvanized Body | |
| -15 | Strainer Extension (DD-50) | |
| -28 | Cast Stainless Steel Body | |
| -S0 | Side Outlet | |






Chart B

| | Std. | P |
|--------------|------------|-------------|
| Pipe Size | No Hub | Push On |
| 2"(51) | 3-5/8"(92) | 4-1/4"(108) |
| 3"(76) | 3-5/8"(92) | 4-1/4"(108) |
| 4"(102) | 3-5/8"(92) | 4-1/4"(108) |
| 6"(152) | 3-1/2"(89) | - |

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

WATTS®

USA: T: (800) 338-2581 • Watts.com **Canada:** T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-FD-1100-A-LR 2433

