Submittal Package

Engineering Specification, Installation, Operation and Maintenance Series LFM115 - Large

Pressure Reducing Control Valve

Sizes: 20 and 24"

A WARNING




Read this Manual BEFORE using this equipment. Failure to read and follow all safety and use information can result in death, serious personal injury, property damage, or damage to the equipment.

Keep this Manual for future reference.

A WARNING

Local building or plumbing codes may require modifications to the information provided. You are required to consult the local building and plumbing codes prior to installation. If the information provided here is not consistent with local building or plumbing codes, the local codes should be followed. This product must be installed by a licensed contractor in accordance with local codes and ordinances.



A WARNING

Need for Periodic Inspection/Maintenance: This product must be tested periodically in compliance with local codes, but at least once per year or more as service conditions warrant. All products must be retested once maintenance has been performed. Corrosive water conditions and/or unauthorized adjustments or repair could render the product ineffective for the service intended. Regular checking and cleaning of the product's internal and external components helps assure maximum life and proper product function.

If installed on a fire sprinkler system, all mechanical checks, such as alarm checks and backflow preventers, should be flow tested and inspected internally in accordance with NFPA 13 and NFPA 25.

Table of Contents	Page
Engineering Specifications	
ACV Schematic	2
Basic Valves	3
Standard Components	7
Optional Components	9
Installation, Operation and Maintenance	
Installation	10



Engineering Specification

LEAD FREE*

Series LFM115 - Large

Pressure Reducing Control Valve


Full Port Ductile Iron Single Chamber Valve

Features

- Throttles to reduce high upstream pressure to constant lower downstream pressure
- · Reducing setpoint is adjustable

Standard Components

- 1 Main Valve M100 Single Chamber
- 2 Pressure Reducing Control LF223
- 3 ACS Adjustable Closing Speed (Globe Valve)
- 4 AOS Adjustable Opening Speed (Globe with Check)
- 5 Pressure Gauges
- X Isolation Cocks
- Y Y-Strainer



Options and Accessories

O L Limit Switch
O P Position Indicator

Operation

The Pressure Reducing Automatic Control Valve (ACV) is designed to automatically reduce a fluctuating higher upstream pressure to a constant lower downstream pressure regardless of varying flow rates. It is controlled by a normally open, pressure reducing pilot designed to: 1) Open (allowing fluid out of the main valve cover chamber) when downstream pressure is below the adjustable setpoint, and 2) Close (allowing fluid to fill the main valve cover chamber) when downstream pressure is above the adjustable setpoint. A decrease in downstream pressure causes the valve to modulate toward an open position, raising downstream pressure. An increase in downstream pressure causes the valve to modulate toward a closed position, lowering downstream pressure.

^{*}The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

M Series Basic Valves

Pressure Reducing Control Valve

Full Port Ductile Iron Single Chamber Basic Valve

This Watts Automatic Control Valve (ACV) is a full port, single chamber basic valve that incorporates a one-piece disc and diaphragm assembly. This assembly is the only moving part within the valve allowing it to open, close, or modulate as commanded by the pilot control system.

Watts ACV Main Valves are Lead Free. The Watts ACV piloting system contains Lead Free* components, ensuring all of our configurations are Lead Free compliant.

Globe Pattern Single Chamber Basic Valve (M100)

Standard Materials

Body and Cover: Ductile Iron ASTM A536

Coating: NSF Listed Fusion Bonded Epoxy

Lined and Coated

Trim: 316 Stainless Steel

Elastomers: Buna-N (standard)

NSF.

Nut, Spring and Stem: Stainless Steel

Anti-Scale: Xylan Coated Stem and Seat (Optional)

Basic Valve Body Options



Globe Flanged

Operating Pressure

150# Flanged = 250psi (17.2 bar) 300# Flanged = 400psi (27.6 bar)

Operating Temperature

Buna-N: 160°F (71°C) Maximum

Epoxy Coating**: 225°F (107°C) Maximum

** Valves can be provided without internal epoxy coating consult factory

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Flow Data


	Valve Size - Inches	11/4	1½	2	2½	3	4	6	8	10	12	14	16	20	24
ted	Maximum Continuous Flow Rate Gpm (Water)	95	130	210	300	485	800	1850	3100	5000	7000	8500	11100	19600	28200
Suggested	Maximum Intermittent Flow Rate Gpm (Water)	119	161	265	390	590	1000	2300	4000	6250	8900	10800	14100	24500	35250
S	Minimum Flow Rate Gpm (Water)	3	5	6	9	15	16	17	25	55	70	190	400		315
ځ	CV Factor GPM (Globe)	26	26	48	75	112	188	387	764	1215	1734	2234	3131		7447
	CV Factor GPM (Angle)	26	27	57	91	125	207	571	889	1530	1945				

- Maximum continuous flow based on velocity of 20 ft. per second.
- Maximum intermittent flow based on velocity of 25 ft. per second.
- Minimum flow rates based on a 20-40 psi pressure drop.
- The C_v Factor of a value is the flow rate in US GPM at $60^{\circ}F$ that will cause a 1psi drop in pressure.
- C_v factor can be used in the following equations to determine Flow
 (Q) and Pressure Drop (ΔP):

Q (Flow) = $C_v \sqrt{\Delta P}$

 ΔP (Pressure Drop) = $(Q/C_v)^2$

- The C_v factors stated are based upon a fully open valve.
- Many factors should be considered in sizing control valves including inlet pressure, outlet pressure and flow rates.
- For sizing questions including cavitation analysis consult Watts with system details.




Valve Cover Chamber Capacity

Valve Size - Inches	20	24
U.S. Gal	25.5	37.1
Liter	96.5	140.4

Valve Travel

Valve Size - Inches	2	0	24			
	in.	cm.	in.	cm.		
Travel - Inches	5.62	14.3	6.75	17.1		

Basic Valve



Item	Description	Material
1	150# Body	Epoxy Coated Ductile Iron - ASTM A536
2	Cover	Epoxy Coated Ductile Iron - ASTM A536
3a	Flange Screws x4	Stainless Steel 18-8
3b	¾ Lock Washer	Stainless Steel - UNS S30400
3c	Flange 1½ NPT, 300 CL	Stainless Steel 18-8
3d	Gasket 1½ Pipe	Buna-N
4a	Guide Cover Screws	Stainless Steel 18-8
4b	Guide Cover	Stainless Steel - UNS S30400
4c	0-Ring	Buna-N - 70 DURO
5	Cover Bearing with O-Ring	ASTM A276 UNS S30400, Buna-N - 70 DURO
6	Stem	Xylan Coated Stainless Steel – UNS S30400
7	Cover Stud with Hex Nut and Flat Washer	ASTM A193 GRB7 Yellow Zinc PLT; ASTM A194 GR2H Yellow Zinc PLT; Carbon Steel Zinc Plated
8	Diaphragm	Buna-N
9	Stem Nut with Set Screw	Stainless Steel ASTM A276 304; Stainless Steel - 18-8
10	Stem Nut Washer	Stainless Steel - UNS S30400
11	Diaphragm Washer	Epoxy Coated Ductile Iron – ASTM A536
12	0-Rings x2	Buna-N
13	Disc Retainer	Epoxy Coated Ductile Iron – ASTM A536
14	Disc	Buna-N
15	Spacer Washer x3	Vulcanized Fiber
16	Disc Guide	CF8M
17	Seat Screws x18	Stainless Steel 18-8
18	Seat	ASTM A743 CF8M
19	0-Ring	Buna-N






NOTICE

Installation: If unit is installed in any orientation other than horizontal (cover up) OR extreme space constraints exist, consult customer service prior to or at the time of order.

Dimensions



Valve Size	Globe	: 150#	Globe	300#	Cover To	o Center	Port Si	ize NPT	Port Si	ze NPT	Port Si	ze NPT	Shipping	Weights*
	1	A		В		С		D		Ē	I			
in.	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kgs.
20	52	1320.8	53%	1361.9	39%	1000	1½	38.1	1½	38.1	1½	38.1	4312	1955.9
24	61½	1562.1	63¼	1606.3	47	1192.8	1½	38.1	1½	38.1	1½	38.1	6629	3006.9

LEAD FREE*

LF223, LF223-S

High Capacity Water Pressure Reducing Valves*

Sizes: 1/2" - 2 1/2" NPT

Series 223 and 223-S High Capacity Water Pressure Reducing Valves are designed to reduce incoming water pressure to a sensible level to protect plumbing system components and reduce water consumption. This series is suitable for water supply pressures up to 300psi (20.7 bar) and may be adjusted from 25 – 75psi (172 – 517 kPa). The standard setting is 50psi (345 kPa). Series 223 features an enlarged diaphragm, spring cage and seat orifice for high capacity performance. Series 223-S has the same options as the 223, except it is furnished with a strainer. All parts are quickly and easily serviceable without removing the valve from the line. The optional bypass feature permits the flow of water back through the valve into the main when pressures, due to thermal expansion on the outlet side of the valve, exceed the pressure in the main supply.



Standard Materials

Body: 1/2" - 2" Bronze

2 1/2" Iron

Seat: Replaceable stainless steel

Diaphragm: Reinforced Buna-N

Valve Disc: EPDM

Specifications

A Lead Free Water Pressure Reducing Valve shall be installed on the water service pipe near its entrance to the building where supply main pressure exceeds 60psi (413 kPa) to reduce it to 50psi (345 kPa) or lower. The water pressure reducing valve shall be constructed using Lead Free* materials. Lead Free* regulators shall comply with state codes and standards, where applicable, requiring reduced lead content. Sill cocks and outside wall hydrants may be left on full main pressure at the option of the owner. Provision shall be made to permit the bypass flow of water back through the valve into the main when pressures, due to thermal expansion on the outlet side of the valve, exceed the pressure in the main supply. Pressure reducing valves with builtin bypass check valves and strainer will be acceptable. Approved valves shall comply with ASSE 1003. Valve shall be a Watts Series LF223 or LF223S (with strainer)


*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.


Dimensions - Weights

SIZE	DIMENSIONS										WEIGHT				
	A (L	.F223)	As (LF	223S)		C		D	N (LF	223S)	LF:	223	LF2	238	
in.	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kgs	lbs.	kgs	
1/2	41/4	108	9	229	61/4	159	2	50	21/2	64	4.5	2.0	6	2.7	
3/4	41/4	108	9	229	61/4	159	2	50	21/2	64	5	2.3	6.5	2.9	
1	43/4	121	1015/16	262	6½	165	21//8	54	2 ¹⁵ / ₁₆	75	7	3.2	9.5	4.3	
11/4	5	127	11 ¹⁵ ⁄16	287	6¾	172	23/4	70	3	76	9	4.1	12	5.4	
11/2	63/4	171	14¾	375	97//8	251	23/4	70	37/16	87	19.5	8.8	23.5	10.7	
2	8	203	16¾	425	10¾	273	3%	86	4	102	30	13.6	37.5	17.0	
21/2	9	229	201//8	511	10¾	273	3%	86	5	127	32.5	14.8	59	26.8	

LF223, LF223-S

High Capacity Water Pressure Reducing Valves*





Item	Description
1	Adjusting Screw
2	Spring Housing
3	Spring
4	Cap Screw
5	Diaphragm
6	Body
7	Bypass Gasket
8	Seat
9	Nut
10	Locking Seal

Item	Description
11	Spring Guide
12	Nut
13	Washer
14	Diaphragm Washer
15	Yoke
16	Disc Screw?
17	Disc
18	0-Ring
19	Disc Holder
20	Bottom Plug


LEAD FREE*

Model 50

Position Indicator

When specified as an option on a Control Valve, the Model 50 Position Indicator is installed in the topmost cover port of the Main Valve and allows for visual indication of valve position. The Model 50 is also very useful during valve start-up and troubleshooting procedures.

A stainless steel indicating rod threads into the tapped portion of the Main Valve stem and moves inside of a cylindrical Pyrex sight tube. The indicating rod travels up and down, following Main Valve stem movement. The housing protects the sight tube and indicating rod, and allows visibility on two sides. The screw driver operated test cock installed on the top of the Model 50 housing provides a controlled method of removal of air from the cover chamber during start-up or troubleshooting of the Main Valve.



Item	Description
1	Test Cock
2	Housing
3	Gasket
4	Pyrex Sight Tube
5	Body
6	Indicating Rod
7	Stem Adaptor (8" or Larger)



Model LF50

Specifications

Standard Material: Stainless Steel Housing and Body

Stainless Steel Indicating Rod

Lead Free Test Cock Pyrex Sight Tube

Optional Material: Stainless Steel Test Cock

Pressure Rating: 400psi (27.6 bar)

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Dimensions

Valve Size	Dimension			
(in)	(in)			
11/4 - 11/2	7%			
2	4%			
2½	4%			
3	4%			
4	5			
6	5			
8	5%			
10	5%			
12	7¼			
14	7¼			
16	7¼			
18*	71/4			
20*	7¼			
24*	7¼			
	*Poducod Por			

*Reduced Port


LEAD FREE*

Model 51


Single Limit Switch

The Model 51 Single Limit Switch provides visual indication of valve position, as well as remote electrical indication of "valve open" or "valve closed". The single pole double throw Micro-Switch can be connected to open or close an electrical circuit when the valve opens or closes.

The adjustable collar is normally set to contact the trip arm when the main valve is closed. The collar can be positioned on the stem by loosening the set-screw to actuate the switch at the desired point of valve travel.



Single Pole Double Throw Switch





Model LF51

Specifications

Body Material: Stainless Steel

Elastomers: Buna-N (standard)

EPDM (optional) Viton™ (optional)

Enclosure: NEMA 1, 3, 4 and 13 General Purpose (standard)

NEMA 1,7 and 9 Explosion Proof (optional)

Electrical: Form C SPDT Switch

15 amp. 125, 250 or 480 VAC

½ amp. 125 VDC ¼ amp. 250 VDC ½" Conduit Connection

Viton™ is a trademark of The Chemours Company FC, LLC

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Parts List

Item	Description
1	Limit Switch
2	Bracket
3	Stem
4	Trip collar
5	Set Screw
6	Сар
7	Wiper Ring*
8	0-Ring*
9	Guide
10	0-Ring*
11	Polypak*
12	Locknut
13	Body
14	Pin
15	Coupling

*Included in Repair Kit

Installation, Operation and Maintenance - Series LFM115 - Large


Installation

- 1. Prior to installation, flush line to remove debris.
- 2. Install valve so the flow arrow matches flow through the line, and gauges to monitor valve inlet and outlet pressures. A Position Indicator can be installed to provide visual indication of valve position and operation without disassembly.
- 3. Install isolation valves upstream and downstream of the main valve.

Note: If using butterfly valves, ensure valve disc does not contact the main valve.

- 4. Provide adequate clearance for valve servicing and maintenance. Refer to valve servicing dimensions on next page.
- 5. Avoid installing valves 6" and larger in the vertical position (main valve stem horizontal). Automatic Control Valves (ACVs) are designed for horizontal in-line installation, with the cover facing up (main valve stem vertical). Slow operation or premature stem and guide wear may occur if valve is not installed according to factory recommendations. Consult factory for detailed engineering review prior to ordering if valve is to be installed other than horizontally in-line.
- 6. If valve is equipped with a pilot control system, extra precautions should be made during installation to protect the piping circuit from damage. Only remove the pilot control system from the valve if necessary. Tubing and fittings should be kept clean, and replaced exactly as removed. Consult appropriate hydraulic schematic to ensure proper re-assembly.

Valve Servicing Dimensions



The following tables detail the recommended minimum valve servicing dimensions.

Globe

Size (in)	20		24	
	in.	ст.	in.	cm.
A (in)	82	209	82	209
B (in)	48	209	82	209

Limited Warranty: Watts Regulator Co. (the "Company") warrants each product to be free from defects in material and workmanship under normal usage for a period of one year from the date of

THE WARRANTY SET FORTH HEREIN IS GIVEN EXPRESSLY AND IS THE ONLY WARRANTY GIVEN BY THE COMPANY WITH RESPECT TO THE PRODUCT. THE COMPANY MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED. THE COMPANY HEREBY SPECIFICALLY DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

The remedy described in the first paragraph of this warranty shall constitute the sole and exclusive remedy for breach of warranty, and the Company shall not be responsible for any incidental, special or consequential damages, including without limitation, lost profits or the cost of repairing or replacing other property which is damaged if this product does not work properly, other costs resulting from labor charges, delays, vandalism, negligence, fouling caused by foreign material, damage from adverse water conditions, chemical, or any other circumstances over which the Company has no control. This warranty shall be invalidated by any abuse, misuse, misapplication, improper installation or improper maintenance or alteration of the product.

Some States do not allow limitations on how long an implied warranty lasts, and some States do not allow the exclusion or limitation of incidental or consequential damages. Therefore the above limitations may not apply to you. This Limited Warranty gives you specific legal rights, and you may have other rights that vary from State to State. You should consult applicable state laws to determine your rights. SO FAR AS IS CONSISTENT WITH APPLICABLE STATE LAW, ANY IMPLIED WARRANTIES THAT MAY NOT BE DISCLAIMED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE LIMITED IN DURATION TO ONE YEAR FROM THE DATE OF ORIGINAL SHIPMENT.



USA: T: (978) 689-6066 • F: (978) 975-8350 • Watts.com Canada: T: (888) 208-8927 • F: (905) 481-2316 • Watts.ca Latin America: T: (52) 55-4122-0138 • Watts.com

© 2022 Watts ES-ACV-LFM115 2217