

Engineering Specification

Job Name _____
 Job Location _____
 Engineer _____
 Approval _____
 Tag _____


Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____

GL Series PDI Certified Grease Interceptor Specifications

Watts Light Commercial GL-Series PDI Certified low-rough-in recessed or floor mounted epoxy coated steel grease interceptor with external flow control fitting and no hub connection.



Options		
Suffix	Description	
-E	Extension	<input type="checkbox"/>
-THD	Threaded Connections	<input type="checkbox"/>



GL-Series

Model #	Flow Rate		Capacity		Pipe Size				Length		Width		Height	
					A		C		D		E		F	
Model	GPM	LPM	lbs.	kg.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
GL-20	20	76	40	18	3	76	4 ¼	108	34 ⅞	864	22 ⅞	581	11 ¾	298
GL-35	35	133	70	32	4	100	4 ½	114	40 ⅞	1016	32 ⅞	835	11 ⅞	302
GL-50*	50	190	100	45	4	100	5 ½	140	55	1397	33	838	14	356

*Not PDI Certified

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • F: (828) 248-3929 • Watts.com
Canada: T: (888) 208-8927 • F: (888) 479-2887 • Watts.ca
Latin America: T: (52) 55-4122-0138 • Watts.com