

Corrosion Resistant Laboratory Sinks





Style	Α	В	С	D	E	F	G	Н	Wt. oz.	
ARLS-11	12	12	8	14.5	14.5	3.5	3.5	11	72	
ARLS-12	16	8	7	18.5	10.5	4	4	9.25	75	
ARLS-13	16	16	8	18.5	18.5	3.5	3.5	11	106	
ARLS-14	18	12	8	20.75	14.75	3	3	10.25	106	
ARLS-15	18	15	12	20.5	17.5	4	4	15	165	
ARLS-16	21	18	10	23.5	20.5	3.5	3.5	12	165	
ARLS-17	23	18	12	25.5	20.5	4	4	14.25	185	
ARLS-18	25	15	10	27.5	17.5	4	4	13	168	
Style	Α	В	С	D	E	F	G	Н	Wt. oz.	
ARLS-13-ADA	16	16	6	18.5	18.5	3.5	3.5	11	98	
ARLS-14-ADA	18	12	6	20.75	14.75	3	3	10.25	101	
ARLS-15-ADA	18	15	6	20.25	17.5	4	4	15	158	

Laboratory Sinks Compliant with the Americans with Disabilities Act (ADA)


The ADA Laboratory sinks meet the standards set forth by the Americans with Disabilities Act. These ADA sinks have a depth of six (6) inches to allow proper clearance of wheel chairs, and have the sink outlet in the rear right hand corner, so piping does not interfere with wheelchairs.

Recommended Specification:


Corrosion Resistant Lab Sink shall be manufactured from virgin High Density Polyethylene conforming to ASTM D 1248 with integral national pipe thread outlet. The waste assembly shall be located in the rear corner of the sink.


^{*}Note: Sinks often ship dimensional weight. Consult freight carrier for details on dimensional weight.

Corrosion Resistant Laboratory Sinks



Style	Α	В	С	D	Е	F	G	Н	I
ARLS-DB-1	12	12	8	30.25	14.5	3.5	3.5	11	3
ARLS-DB-2	15	18	10	41.25	17.5	3.5	3.5	13	3





	Α	В	С	D	Е	F	G	Н	J	K	L	М	N
ARLS-CDE	3 18	15	10	49	30	3	211/16	25/8	7	5	83/16	4	13//8

Tanks, Sinks, & Monitors ORION FITTINGS, INC. 5