



TOP ACCESS
OPENING



HEAT EXCHANGER DESIGN STANDARDS			
	MAX. WORKING PRESS. (PSIG)	MAXIMUM TEMP. (°F)	TEST PRESS. (PSIG)
SHEEL SIDE	150	210	225

ASME B & PV CODE: SECTION IV STAMP HLW




8.24 [21]

4.24 [11]

4X SLOTS $\phi 0.50$ [$\phi 1$]
FOR ANCHOR BOLTS

4X ANCHOR BOLT ACCESS OPENINGS



- NOTES:
- 1) ALL DIMENSIONS SHOWN ARE IN INCHES (CENTIMETERS).
 - 2) STANDARD PRODUCT COMES WITH ONE T&P VALVE FOR MODELS LESS THAN 700 MBH. FOR MODELS 700 MBH AND GREATER, A SECOND RELIEF VALVE WILL BE PROVIDED AS SHOWN.
 - 3) PVI RESERVES THE RIGHT TO MODIFY WATER HEATER DIMENSIONS WITHOUT PRIOR NOTICE.

 PVI INDUSTRIES
FORT WORTH, TEXAS

CONQUEST 400-1200 MBH
GAS FIRED WATER HEATER
DIMENSIONAL DRAWING

DWN.BY <u>K.S.</u> DATE <u>071823</u>	AP-P-1094	REV. B
SCALE <u>NTS</u>		
REV.BY <u>K.S.</u> DATE <u>020725</u>		