

# Engineering Specification

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_

Approval \_\_\_\_\_

Representative \_\_\_\_\_


Tag \_\_\_\_\_

## G Series Floor Mounted Grease Interceptor Specifications

Watts Light Commercial G Series epoxy coated steel floor mounted grease interceptor with internal flow control, and no hub connections.



Options		
Suffix	Description	
-THD	Threaded Connections	<input type="checkbox"/>



**G Series**

Model #	Flow Rate		Capacity		Pipe Size				Length		Width		Height	
					A		C		D	E	F			
	GPM	LPM	lbs.	kg	in	mm	in	mm	in	mm	in	mm	in	mm
G-84	4	15.2	8	3.6	2	50	3	76	10	254	10	254	10	254
G-147	7	26.6	14	6.4	2	50	3	76	11¼	298	11¼	298	11	279
G-2010	10	38.0	20	9.0	2	50	3	76	13½	343	13½	343	12	305
G-3015	15	57.0	30	13.6	2	50	3	76	15¼	387	15¼	387	13	330
G-4020	20	76.0	40	18.2	3	80	3½	90	17	432	17	432	14½	368

### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



**USA:** T: (800) 338-2581 • F: (828) 248-3929 • Watts.com

**Canada:** T: (888) 208-8927 • F: (888) 479-2887 • Watts.ca

**Latin America:** T: (52) 55-4122-0138 • Watts.com